

Pt100 Industrial Sensor Probe, Class B

Available in 3mm or 6mm diameter x 150mm or 250mm probe lengths



- Multipurpose Pt100 Probe to IEC751
- Class B, 4-wire connection
- Rigid 316 stainless steel sheath, 3.0mm or 6.0mm diameter
- 1 metre Teflon® insulated, screened lead
- Sensor temperature rating -50°C to +250°C

Specifications

Sensor type: Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Construction: 3.0mm or 6.0mm diameter 316 stainless steel sheath.
Probe temperature range: -50°C to +250°C
Extension cable: 1 metre flexible Teflon® insulated, screened
Termination: 4-wire tails – allows connection to any PT100 instrument 2, 3 or 4 wire

Probe Diameter	Probe Length	Cable Conductors	Manufacturer's Part Number	Rapid Part Number
3mm	150mm	7/0.1mm	XE-3602-001	61-3208
3mm	250mm	7/0.1mm	XE-3604-001	61-3209
6mm	150mm	7/0.2mm	XE-3622-001	61-3210
6mm	250mm	7/0.2mm	XE-3624-001	61-3211