

## Pt100 Tubular Ceramic Insert Elements with tail wires





- Tubular ceramic encased Pt100 elements
- Thin film Pt100 element housed/potted in a ceramic sheath, 5mm dia. x 35mm long
- Class 'B' to IEC 751: 2008
- Single element, 2 or 4 wire configurations
- Available with stranded 7/0.2mm silver plated copper PFA Teflon<sup>®</sup> insulated leads
- 50 or 450mm lead lengths
- Sensor temperature rating: -50°C to +250°C PFA Teflon<sup>®</sup> types

## **Ordering information:**

Ceramic	No. of	Lead/Wire	Lead	Manufacturer's	Rapid
Length	Wires	Type	Length	Part Number	Part Number
35mm	2 wire	7/0.2mm SPC Teflon	50mm	XE-3666-001	61-3213
35mm	4 wire	7/0.2mm SPC Teflon	450mm	XE-3667-001	61-3214

