


Glassfibre Insulated Flat Pair





- Glassfibre insulated extension cable in thermocouple type K
- Glassfibre insulated flat pair construction, conductors laid flat, Glassfibre insulated with Glassfibre overall, silicone varnished throughout
- Good temperature resistance but not suitable where fluids are present
- Types K available in solid 1/0.3mm conductors
- Available in 25 or 50 metre reel lengths
- All types; conductors are made from associated K, J or T thermocouple alloy type
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3

Calibration Type	No. of Strands	Colour	Product Code	Part Number	Rapid Part Number
К	1/0.315 mm	Туре К	25M - K 1/0.315 F/G F/P IEC	XE-2163-025	61-3246
К	1/0.315 mm	Туре К	50M - K 1/0.315 F/G F/P IEC	XE-2163-050	61-3247

Overall sheath Dimensions (approx.)				
1/0.3mm	1.1mm x 1.7mm			

Loop resistance (ohms per combined metre) Type K @ 14.1 Ohms/mtr

