



APPLIANCE WIRING MATERIAL

Subj.758

Section 2

Page 2651

Issued:1973-08-13

Revised:2013-02-27

Style 2651

Flat Cable.

Rating	105 deg C, 300 Vac, Horizontal flame.
Conductor	36 AWG - 14 AWG, solid or stranded.
Insulation	Extruded PVC or heat laminated PVC, 9 mils minimum average thickness, 7 mils minimum thickness at any point.
Assembly	Two - 150 conductors. Top or bottom layers may form ridges. Sections of the cable may be split into singles or groups of conductors.
Shield	Optional.
Covering	Optional. Extruded PVC, 5 mils minimum thickness at any point, 80 mils maximum thickness.
Standard	Appliance Wiring Material UL 758.
Marking	General.
Use	Internal wiring of Electronic equipment.

UL and the UL Logo are trademarks of UL LLC © 2018