Actuator Magnets

AS1010 Magnets

Actuator Magnet in Threaded Aluminum Housing



Features

- Rugged aluminum housing
- · Adjustable threaded mounting stud
- RoHS compliant
- Typical air gap of 1.5 mm

Environmental Specifications

Operating Temperature	-40 °C to 150 °C (-40 °F to 302 °F)
Storage Temperature	-40 °C to 150 °C (-40 °F to 302 °F)

Products

Part Number Magnet Material Active Sensing		Active Sensing Face	Face	
AS101001	Alnico	South		
AS101002	Alnico	North		
AS101003	Samarium Cobalt	South		

Dimensions mm (inches)



