

Specifications:

Rating: 300mA
 Insulation Resistance: DC 500V 100M ohm minimum
 Dielectric Strength: AC 1500V 1 minute
 Operation Temperature: -20°C~+80°C

Material:

Handle: ABS
 Clip: Phosphor bronze

Fits O.D. less than $\varnothing 2\text{mm}$ wire by soldering

