

Specification:

Max working voltage: 50V
 Max current rating: 1Amp (AC)
 Insulation resistance: 100MΩ @ 500Vdc
 Dielectric strength: 1000Vac/1 Min



Colour	Order code	Dimensions (mm)			
		A	B	C	D
Red	17-0270	48±0.5	57±0.5	ø9.5±0.2	ø12±0.3
Black	17-0290				

