

Tinned copper wires available on bandoliered tape with equivalent spacing to the CR25 resistor range.

Specification:

Material:	Soft copper wire with tin plating
Conductor resistance:	0.005mΩ/mm ²
Tension strength:	CNS 8938 28kg/mm ²
Extension rate:	CNS 8938 26°
Conductivity:	Minimum 96%
Twist strength:	CNS 8938 3 cycles
Solderability 95%:	JIS520 260°C ±5°C
Element of plating:	Tin 100%
Plating thickness:	3-5μ
Current rating at 70°C:	0.6mm – 7.5A



Order code	Quantity
62-0472	Packs of 1,000
62-0478	Full reels of 10,000

