


TABLE A

**RoHS COMPLIANT**

**SPECIFICATIONS:**  
 1. RATING: 11V AC 1A MAX  
 OR 12V DC 2A MAX.  
 2. INSULATION RESISTANCE:  
 50M OHM MIN AT 500V DC.  
 3. DIELECTRIC STRENGTH:  
 500V AC / 1 MINUTE.



	7.0ø BACK SHELL
	6.0ø BACK SHELL
X	5.0ø BACK SHELL (STANDARD)
	COVER DIM.

TABLE A

**MATERIAL:**  
 A. COVER: PE+2L  
 B. SHELL: ABS  
 C. METAL SHIELD:  
 BRASS NICKEL PLATED  
 D. HOUSING: NYLON66+CF  
 E. CONTACT:  
 BRASS SILVER PLATED