


**AMP SOLISTRAND**

Ringzungen,  
6,7–304,0 mm<sup>2</sup>



**AMP SOLISTRAND**

Ring Tongues,  
6.7–304.0 mm<sup>2</sup>

Leiterquerschnittsbereich 10,0 mm<sup>2</sup>  
AWG 8 (6,7–10,5 mm<sup>2</sup>)

Wire Size Range 10.0 mm<sup>2</sup>  
AWG 8 (6.7–10.5 mm<sup>2</sup>)

Bolzen Bolt M	Bolzenloch Stud Hole (mm)	Abmessungen/Dimensions (mm)					Bestell-Nummer Part Number	Werkzeug Tooling
		S	W	C min.	L	E		
5.0	5.2	1.2	11.9	9.1	23.7	17.7	160013-0	
6.0	6.1	1.2	11.9	9.1	23.8	17.9	130550-0	
6.0	6.7	1.2	11.9	9.1	23.7	17.7	33461-0	siehe Seiten 22-63–22-78 see pages 22-63–22-78
8.0	8.3	1.2	15.1	13.5	29.7	22.1	33462-0	
10.0	10.5	1.2	15.1	13.5	29.7	22.2	160056-0	
12.0	13.0	1.2	31.8	25.4	49.9	34.0	35664-0	

Leiterquerschnittsbereich 16,0 mm<sup>2</sup>  
AWG 6 (10,6–16,7 mm<sup>2</sup>)

Wire Size Range 16.0 mm<sup>2</sup>  
AWG 6 (10.6–16.7 mm<sup>2</sup>)

Bolzen Bolt M	Bolzenloch Stud Hole (mm)	Abmessungen/Dimensions (mm)					Bestell-Nummer Part Number	Werkzeug Tooling
		S	W	C min.	L	E		
5.0	5.2	1.45	11.9	13.5	29.7	23.7	130552-0	
6.0	6.3	1.45	11.9	13.5	29.7	23.7	130554-0	
6.0	6.7	1.45	15.9	13.5	31.8	23.8	33465-0	siehe Seiten 22-63–22-78 see pages 22-63–22-78
8.0	8.3	1.45	15.9	13.5	31.6	23.7	33466-0	
10.0	10.3	1.45	15.9	13.5	31.6	23.7	160032-0	
12.0	13.0	1.45	22.2	25.4	46.7	35.9	320344-0	
12.0	13.1	1.45	31.8	25.4	51.6	35.6	36808-0	

Leiterquerschnittsbereich 25,0 mm<sup>2</sup>  
AWG 4 (16,8–26,6 mm<sup>2</sup>)

Wire Size Range 25.0 mm<sup>2</sup>  
AWG 4 (16.8–26.6 mm<sup>2</sup>)

Bolzen Bolt M	Bolzenloch Stud Hole (mm)	Abmessungen/Dimensions (mm)					Bestell-Nummer Part Number	Werkzeug Tooling
		S	W	C min.	L	E		
5.0	5.2	1.8	16.7	13.1	33.3	25.0	160119-0	
6.0	6.1	1.8	16.7	13.1	33.2	24.9	130560-0	
6.0	6.7	1.8	12.7	11.1	30.5	24.1	33469-0	siehe Seiten 22-63–22-78 see pages 22-63–22-78
8.0	8.3	1.8	16.7	13.1	33.2	24.9	33470-0	
10.0	10.5	1.8	16.7	13.1	33.2	24.9	160075-0	
12.0	13.0	1.8	22.2	25.4	48.3	37.2	327175-0	
12.0	13.1	1.8	31.8	25.4	53.1	37.1	35668-0	
16.0	16.6	1.8	31.8	25.4	53.1	37.2	35669-0	

Leiterquerschnittsbereich 35,0 mm<sup>2</sup>  
AWG 2 (26,7–42,4 mm<sup>2</sup>)

Wire Size Range 35.0 mm<sup>2</sup>  
AWG 2 (26.7–42.4 mm<sup>2</sup>)

Bolzen Bolt M	Bolzenloch Stud Hole (mm)	Abmessungen/Dimensions (mm)					Bestell-Nummer Part Number	Werkzeug Tooling
		S	W	C min.	L	E		
6.0	6.3	1.8	15.9	17.4	38.8	30.9	130562-0	
6.0	6.7	1.8	22.6	17.5	42.1	30.8	320138-0	
8.0	8.3	1.8	15.9	17.4	38.8	30.9	322870-0	siehe Seiten 22-63–22-78 see pages 22-63–22-78
8.0	8.3	1.8	22.2	17.5	42.2	30.2	35183-0	
10.0	10.5	1.8	22.2	17.4	42.0	30.9	160002-0	
12.0	13.0	1.8	22.2	17.4	42.0	30.9	35185-0	
16.0	16.6	1.8	32.0	34.1	63.7	49.8	320754-0	