



NO	DESCRIPTION	MATERIAL	PLATING
1	BODY	BRASS	GOLD
2	DIELECTRIC	TEFLON	--
3	CENTER PIN	PHOSPHOR BRONZE	GOLD
4	PRESS FIT WASHER	BRASS	GOLD

Dimensions Are In Millimeters  
Unless Otherwise Specified

Tolerances

0.5-6	=	± 0.2
6-30	=	± 0.4
30-120	=	± 0.6
120-315	=	± 1.0
315-1000	=	± 1.6
1000-2000	=	± 2.4

RoHS COMPLIANT

0605040

P/N SC225CU-XGGT50

734212/0414080

SMC JACK TO BNC JACK