



Material:

- Rings & Ribs Steel wire BL1-195(C1008)
- Surface Treating
Nickled-chrome electro plating surface, bright colour
- Comply with the limits as set by RoHS/SVHC
- Weld Joints Contact Strength
Spot welding Points to withstand minimum 88lbs (40Kgs.)

Order code	Fan size	Dimensions (mm)					Number of rings
		A	B	C	ød (id)	øe	
37-0815	40	39.1	33.3	3.8	4.6	1.4	2
37-0817	50	48.9	42.0	4.8	4.6	1.6	3
37-0820	60	57.6	51.2	4.5	4.6	1.7	4
37-0825	80	79.1	72.9	5.7	4.6	1.7	5
37-0830	90	90.2	83.6	5.7	4.6	1.7	6
37-0835	120	115.5	105.6	5.7	4.6	1.7	8