


5

4

3

2

1



	Bestell-Nummer / PART NO		$\phi$	Leiterquerschnitt		Abisolierlänge der Litze	Kennzeichnung identification	
	versilberl silverplated	vergoldet goldplated		mm <sup>2</sup>	AWG			
C Stiftkontakt male contact	09 33 000 6127	09 33 000 6117	0,90	0,14-0,37	26-22	7,5	keine Rille / no groove	1)
	09 33 000 6121	09 33 000 6122	1,15	0,5	20		keine Rille / no groove	
	09 33 000 6114	09 33 000 6115	1,3	0,75	18		1 Rille / 1 groove ①	
	09 33 000 6105	09 33 000 6118	1,45	1	18		1 Rille / 1 groove	
	09 33 000 6104	09 33 000 6116	1,75	1,5	16		2 Rillen / 2 grooves	
	09 33 000 6102	09 33 000 6123	2,25	2,5	14		3 Rillen / 3 grooves	
	09 33 000 6106		2,55	3	12		1 breite Rille / 1 wide groove	
	09 33 000 6107	09 33 000 6119	2,85	4	12		keine Rille / no groove	
B Buchsenkontakt female contact	09 33 000 6227	09 33 000 6217	0,90	0,14-0,37	26-22	7,5	keine Rille / no groove	1)
	09 33 000 6220	09 33 000 6222	1,15	0,5	20		keine Rille / no groove	
	09 33 000 6214	09 33 000 6215	1,3	0,75	18		1 Rille / 1 groove ①	
	09 33 000 6205	09 33 000 6218	1,45	1	18		1 Rille / 1 groove	
	09 33 000 6204	09 33 000 6216	1,75	1,5	16		2 Rillen / 2 grooves	
	09 33 000 6202	09 33 000 6223	2,25	2,5	14		3 Rillen / 3 grooves	
	09 33 000 6206		2,55	3	12		1 breite Rille / 1 wide groove	
	09 33 000 6207	09 33 000 6221	2,85	4	12		keine Rille / no groove	

1) Nur für Buchanan Crimpwerkzeug  
Einstell  $\phi 1,0$   
only for Buchanan crimping tool adjusting  $\phi 1,0$

			All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse / Free size tolerances																
						<table border="1"> <tr> <td></td> <td>Dat.</td> <td>Name</td> <td rowspan="3">Massstab / Scale</td> </tr> <tr> <td>Detail.</td> <td>11.12.92</td> <td>PENNER</td> </tr> <tr> <td>Insp.</td> <td></td> <td>HERB</td> </tr> <tr> <td>Stand.</td> <td></td> <td></td> <td>2:1</td> </tr> </table>				Dat.	Name	Massstab / Scale	Detail.	11.12.92	PENNER	Insp.		HERB	Stand.			2:1	Han E Kontakte gedreht 16A/ Han E contacts twisted 16A		
	Dat.	Name	Massstab / Scale																						
Detail.	11.12.92	PENNER																							
Insp.		HERB																							
Stand.			2:1																						
			<table border="1"> <tr> <td>411037</td> <td>18.05.04</td> <td>Loe.</td> </tr> <tr> <td>19122</td> <td>24.11.95</td> <td>KR</td> </tr> <tr> <td>15087</td> <td>24.03.93</td> <td>ZILK</td> </tr> </table>			411037	18.05.04	Loe.	19122	24.11.95	KR	15087	24.03.93	ZILK	HARTING Electric GmbH & Co. KG D-32339 Espelkamp 			TB 09 33 000 6... Sub. TB 09 33 000 6... v.17.03.92							
411037	18.05.04	Loe.																							
19122	24.11.95	KR																							
15087	24.03.93	ZILK																							
Bestell Nr / Part No			Mod. Dat. Name						Blatt / page																