SOLDERPOTS



DATA SHEET

Antex part number CM82060



- Suitable for tinning component leads, wires, tags etc
- Detachable tray surrounds crucible, retains excess dross when cleaning solder surface
- Pot seated on ceramic and nylon base 120mm x 120mm with four holes, fixing centres 100mm x 100mm, for bench fixing
- Heating element sets available separately

SPECIFICATIONS SOLDERPOT MAX

TYPE SOLDER POTS

TYPICAL OPERATING TEMPERATURE 385°C SOLDER CAPACITY 140 g AVAILABLE WATTAGE 90W AVAILABLE VOLTAGE 230V AVAILABLE PLUG BP

FREQUENCY 50Hz / 60Hz

BASE CERAMIC AND NYLON

CRUCIBLE DIAMETER 39mm
DEPTH 126mm
MAINS CABLE LENGTH 1.5m

SOLDER SUITABILITY LEAD FREE SOLDER

FIXING HOLES 4