

UT33A



Palm-Size Digital Multimeters

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/400V/500V	±(0.8%+1)
AC Voltage	4V/40V/400V/500V	±(1.2%+3)
DC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1%+2)
AC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1.5%+5)
Resistance	400Ω/4kΩ/40kΩ/400kΩ/4MΩ/40MΩ	±(1%+2)
Special Functions		
Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
Transistor		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	Around 10MΩ	
Max. Display	3999	

GENERAL CHARACTERISTICS

Power	1.5V Battery (AAA x 2)
LCD Size	48 x 16mm
Product Colour	Red and Grey
Product Net Weight	156g
Product Size	130 x 73.5 x 35mm
Standard Accessories	Test Lead, Battery, English Manual, Holster
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	60pcs
Standard Carton Measurement	490 x 356 x 315mm (Around 0.055 CBM Per Standard Carton)
Standard Carton Gross Weight	18kg

Specifications and other information are subject to change without further notice.