

UT321



Digital Thermometers

SPECIFICATIONS

Basic Functions	UT321
Temperature -200.0°C to + 1372°C (K-Type) -328.0°F to + 2501°F	✓
Temperature -210.0°C to + 1200°C (J-Type) -346.0°F to + 2192°F	✓
Temperature -250.0°C to + 400.0°C (T-Type) -418.0°F to + 752.0°F	✓
Temperature -150.0°C to + 1000°C (E-Type) -238.0°F to + 1832°F	✓
Temperature Best Accuracy	K,J,T,E-Type: 0.5% ± 0.8°C
Display Resolution	0.1°C (when > 999.9°C : 1°C)
T1 input	✓
°C/ °F/ K Selection	✓
Data Logging	100
USB Data Transfer	✓
User Setup	✓
Temperature Data Hold	✓
Electricity Cut Off Memory	✓
MAX / MIN / AVG temperatures	✓
Display Backlight	✓
Sleep Mode	✓
Low Battery Display	✓

GENERAL CHARACTERISTICS

Power	USB (Auto Double White Display Backlight) or 9V Battery (6F22)
LCD Size	30 × 32mm
Product Color	Red and Grey
Product Net Weight	270g
Product Size	175 × 85 × 30mm
Standard Accessories	Battery, English Manual, USB Cable, Software, K Type Temperature Probe
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40pcs
Standard Carton Measurement	460 x 390 x 270mm (0.048 CBM Per Standard Carton)
Standard Carton Gross Weight	21kg

Specifications and other information are subject to change without further notice.