

UT325

Digital Thermometers

SPECIFICATIONS


[Enlarge](#)
[Download Manual](#)
[Download Software](#)

| Basic Functions | UT325 |
|---|--|
| Temperature -200.0°C to +1372°C (K-Type) -328.0°F to +2501°F | ✓ |
| Temperature -210.0°C to +1200°C (J-Type) -346.0°F to +2192°F | ✓ |
| Temperature -250.0°C to +400.0°C (T-Type) -418.0°F to +752.0°F | ✓ |
| Temperature -150.0°C to +1000°C (E-Type) -238.0°F to +1832°F | ✓ |
| Temperature 0.0°C to +1767°C (R-Type) +32°F to +3212°F | ✓ |
| Temperature 0°C to +1767°C (S-Type) +32°F to +3212°F | ✓ |
| Temperature -200°C~ +1300°C (N-Type) -328.0°F to +2372°F | ✓ |
| Temperature Best Accuracy | K,J,T,E-Type: 0.2% ± 0.6°C R,S Type: 0.2% ± 2°C N-Type: 0.2% ± 1.5°C |
| Display Resolution | 0.1°C(When > 999.9°C : 1°C) |
| T1, T2 input | ✓ |
| °C/ °F/ K Selection | ✓ |
| High/Low Alarm | ✓ |
| High/Low Signal Output | ✓ |
| User Self-Calibration | ✓ |
| Data Logging | 100 |
| USB Data Transfer | ✓ |
| User Setup | ✓ |
| Temperature Data Hold | ✓ |
| Electricity Cut Off Memory | ✓ |
| MAX / MIN / AVG temperatures | ✓ |
| Sleep Mode | ✓ |
| Low Battery Display | ✓ |

GENERAL CHARACTERISTICS

| | |
|-------|--|
| Power | USB (Auto Double White Display Backlight) or 9V Battery (6F22) |
|-------|--|

| | |
|------------------------------|--|
| LCD Size | 30 × 32mm |
| Product Color | Red and Grey |
| Product Net Weight | 270g |
| Product Size | 175 × 85 × 30mm |
| Standard Accessories | Battery, English Manual, USB Cable, Software, K Type Temperature Probe |
| Standard Individual Packing | Gift Box |
| Standard Quantity Per Carton | 40pcs |
| Standard Carton Measurement | 460 x 390 x 270mm (0.048 CBM Per Standard Carton) |
| Standard Carton Gross Weight | 21kg |

Specifications and other information are subject to change without further notice.

[Back to main menu](#)