Laser Line 400V

Product no.: FT91002699N





- > The Constant flow conrol (CFC) guarantees a optimal air flow regulation independent of the filter polution rate.
 - > Efficiency test via USB port
 - Electronic filter control with optical and acoustical filter alarm
 - Laser extraction unit for laser marking, grinding, cutting, welding with high dust amount.

For this purpose, we recommend:







Soldering irons



Cleaning



Pre-heating plates



Dimensions L x W x H (mm)	441 x 441 x 1020
Dimensions L x W x H (inches)	17,4 x 17,4 x 40,1
Weight (approx.) in kg	51
Voltage	230 V, 50/60 Hz
Power	460 VA
Noise level (distance 1 m) dB(A)	< 53 dB (A)
Max. vacuum	3000 Pa
Capacity m³/h	
Pre-filter	
Compact filter	
Max. capacity	
RS232 interface (remote control)	All system functions can be operated and remotely monitored via the RS232 port
USB port	The USB port can be used to load firmware updates, run efficiency tests and logdat data.
WX-compatible	

Owning the bench









EREM

XCELITE

Phone: +49 (0) 7143 / 580-0 Fax.: +49 (0) 7143 / 580-108 Email: info@weller-tools.com Web: www.weller-tools.com