

ESS280RV

1/3 Sheet Sander

Features

- Ideal for light to medium weight applications such as fine finishing and paint removal
- Variable speed (7,000-12,000 rpm) to optimise surface finish
- Powerful 280W motor for maximum performance
- 1/3 sheet rectangular base ideal for sanding closer to edges and over larger surfaces
- Sand paper attaches through either quick fit hook and loop system or manual clamps for added versatility
- Cyclonic action dust box for efficient dust collection
- Livetool Indicator™ glows blue when plugged into the power supply



SPECIFICATION (1)	ESS280RV
Diameter of orbit (mm)	2
Sanding pad size (mm)	93 x 185
Sound pressure level (dB(A))	91.3
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	102.3
Sound power level uncertainty [dB[A]]	3
Vibration level [m/s ²]	8.6
Vibration uncertainty [m/s ²]	1.5
Supplied in	Tool bag
Oscillation rate (opm)	7,000-12,000
Article Number	5133000535
Weight (kg)	1.7
Power input (W)	280