

RAD1801M

18V Right Angle Drill

Features

- Cordless Angle Drill ideal for working in tight and awkward corners
- Keyless 10mm chuck, for simple bit changes
- Automatic spindle lock for one-handed bit change
- LED lights up your work area for better visibility
- Magnetic drill bit tray for easy storage and access to your drill bits
- Variable speed, reverse and brake for total control of your tool



SPECIFICATION (1)	RAD1801M
Sound pressure level (dB(A))	67.5
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	78.5
Sound power level uncertainty [dB[A]]	3
Vibration screw driving [m s ²]	0.3
Vibration screw driving uncertainty [m s ²]	1.5
Vibration drilling into Metal [m s ²]	1.2
Vibration drilling into metal uncertainty [m s ²]	1.5
No load speed gear 1 (rpm)	0-1100
Voltage (V)	18
Battery pack capacity (Ah)	-
Battery type	-
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Article Number	5133001167
Weight with battery pack (kg)	1.83
Max drilling steel (mm)	10
Max. drilling wood (mm)	38
Chuck capacity (mm)	10