

R18IW3-0

Features

- 18V high power motor delivers 400Nm of torque ideal for fast tightening/removing of heavy duty fasteners.
- Impact Mechanism allows for high amounts of torque with little reactionary feedback through the handle.
- Tri-Beam LED lights eliminate shadows on bits and fasteners even in the darkest work areas.
- 3 speed settings provide added control and versatility.
- Mode 1: 0-2,100 rpm for precision work
- Mode 2: 0-2,500 rpm for added control which helps prevent damage to fasteners and materials
- Mode 3: 0-2,900 rpm for maximum performance for the toughest applications
- 1/2" Square drive with locking pin for easy socket fitment
- Includes 1/4" hex adapter to fit screw driver bits



- Fit up to 100 wheels per charge when combined with our high capacity Lithium+ 4.0Ah battery RB18L40

SPECIFICATION (1)

	R18IW3-0
No load speed (rpm)	0-2900
Max. torque (Nm)	400
Voltage (V)	18
Battery pack capacity (Ah)	-
Impact rate (ipm)	0-3200
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Article Number	5133002436
Weight with battery pack (kg)	2.00