

RWSL1801M

18V Circular Saw

Features

- Ideal for making long straight cuts, trimming sheet wood to size, cutting kitchen work tops, flooring or to make quick and accurate cross cuts in timber.
- Impressive cut capacities 45mm at 90°, 32mm at 45°
- Tool less depth and bevel adjustments make it quick and easy to set up the saw
- Dust port helps you to work in a dust free environment by connecting to a vacuum
- Premium Thin Kerf 150mm blade with 18 carbide tipped teeth provides superb performance and cut quality



SPECIFICATION (1)	RWSL1801M
Sound pressure level (dB(A))	87
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	98
Sound power level uncertainty [dB[A]]	3
Bore size (mm)	10
Vibration cutting wood [m s ²]	1.8
Vibration cutting wood uncertainty [m s ²]	1.5
Vibration cutting metal [m s ²]	1.7
Vibration cutting metal uncertainty [m s ²]	1.5
No load speed (rpm)	0-4,700
Voltage (V)	18
Battery pack capacity (Ah)	-
Battery type	-
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Blade diameter (mm)	150
Article Number	5133001165
Bevel capacity (°)	50
Weight with battery pack (kg)	2.93
Max. cutting depth 45<special id ="5" /> (mm)	32
Max. cutting depth 90<special id ="5" /> (mm)	45