

RRS1801M

18V Reciprocating Saw

Features

- Universal saw for cutting a variety of materials
- Tool-less blade clamp for quick and easy blade changes
- Variable speed and brake
- 22mm stroke length
- Anti vibration technology
- Adjustable shoe increases blade life



SPECIFICATION (1)	RRS1801M
Sound pressure level (dB(A))	81.5
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	92.5
Sound power level uncertainty [dB[A]]	3
Vibration cutting wood [m s ²]	17.9
Vibration cutting wood uncertainty [m s ²]	1.5
Vibration cutting wooden beam [m s ²]	17
Vibration cutting wooden beam uncertainty [m s ²]	1.5
No load speed (rpm)	3100
Voltage (V)	18
Battery pack capacity (Ah)	-
Battery type	-
Supplied in	Gift box, Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Article Number	5133001163
Weight with battery pack (kg)	2.33
Max. cutting capacity wood (mm)	180
Stroke length (mm)	22