

R18AG-0

18V Angle Grinder

Features

- Cordless grinder with 115mm disk ideal for a variety of cutting and grinding applications
- 3 position handle for better control when grinding or cutting
- Two stage non lockable switch for enhanced user protection preventing accidental start up
- Easy to adjust tool-less wheel guard
- Spindle lock for easy accessory changing
- GripZone™ overmould technology for improved comfort with a positive grip



SPECIFICATION (1)	R18AG-0
Sound pressure level (dB(A))	80
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	91
Sound power level uncertainty [dB[A]]	3
Wheel size (mm)	115
Vibration level [m/s ²]	6.9
Vibration uncertainty [m/s ²]	1.5
Bore size (mm)	22
No load speed (rpm)	7500
Voltage (V)	18
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Spindle size	M14
Article Number	5133001903
Weight with battery pack (kg)	2.58