

CCG1801MHG

18V Caulking Gun

Features

- Produces high force for high viscosity materials
- Switch lock helps prevent accidental start-ups
- Variable speed adjustment lever for flow control
- Easy release manual push rod for quick reloading
- Durable gears and carriage frame help ensure tool longevity
- On-board puncture tool to brake tube seal if needed
- GripZone™ overmould technology for improved comfort with a positive grip



SPECIFICATION (1)	CCG1801MHG
Sound pressure level (dB(A))	52
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	63
Sound power level uncertainty [dB[A]]	3
Vibration level [m s²]	2.5
Vibration uncertainty [m s²]	1.5
Voltage (V)	18
Charger supplied	–
No. of batteries supplied	0
No load speed high	6
No load speed low	1
Max ouput force	225
Article Number	5133000192
Weight with battery pack (kg)	2.13