

ROS300

Random Orbit Sander

Features

- Random orbital sander delivers the perfect combination of quick stock removal and fine surface finish
- Ideal for light to medium weight applications such as fine finishing and paint removal
- Powerful 300W motor for maximum performance
- Variable speed (7,000-12,000 rpm) to optimise surface finish
- Quick fit hook and loop sanding sheet attachment
- Cyclonic action dust box for efficient dust collection
- Livetool Indicator™ glows blue when plugged into the power supply



SPECIFICATION (1)	ROS300
Diameter of orbit (mm)	2.4
Sanding pad size (mm)	125
Sound pressure level (dB(A))	88.6
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	99.6
Sound power level uncertainty [dB[A]]	3
Vibration level [m/s ²]	14.68
Vibration uncertainty [m/s ²]	1.5
No load speed (rpm)	7,000-12,000
Supplied in	-
Article Number	5133001145
Weight (kg)	1.7
Power input (W)	300