

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Angle Grinder

GWS 7-115 Professional

Smallest grip circumference and powerful 720 watts

The most important data

| | |
|-------------------|------------|
| Rated power input | 720 W |
| No-load speed | 11.000 rpm |
| Disc diameter | 115 mm |

**Part number:** 0 601 388 106

* Price including VAT

Technical Data

| | |
|------------------------------|------------|
| Battery and power | |
| Rated power input | 720 W |
| Power output | 300 W |
| Performance data | |
| No-load speed | 11.000 rpm |
| Grinding spindle thread | M 14 |
| Disc diameter | 115 mm |
| Rubber backing pad, diameter | 115 mm |
| Wire cup brush, diameter | 75 mm |
| Switch | 2-way |
| Size and weight | |
| Weight | 1,9 kg |

Noise/vibration information

| | |
|-----------------------------|----------------------|
| Surface grinding (roughing) | |
| Vibration emission value ah | 6,5 m/s ² |
| Uncertainty K | 1,5 m/s ² |
| Sanding with sanding sheet | |
| Vibration emission value ah | 3,5 m/s ² |
| Uncertainty K | 1,5 m/s ² |
| Noise | |
| Sound pressure level | 91 dB(A) |
| Sound power level | 102 dB(A) |
| Uncertainty K | 3 dB |

Power tools for trade & industry
Advantages

- Smallest grip circumference (176 mm) compared to other angle grinders in its wattage class for particularly comfortable working
- Powerful 720 watt motor and a weight of only 1.9 kg for continuous use
- Flat gear head for comfortable working, even in tight spaces
- Restart protection - prevents the tool from automatically starting up after a power cut
- Specially developed air inlets ensure optimum motor cooling for a longer lifetime
- Anti-rotation protective guard for a high level of user protection


Prices / Scope of delivery

| Part number: | with accessory set, (Voltage 110 V) | with accessory set, (Voltage 240 V) |
|--|-------------------------------------|-------------------------------------|
| Protective guard 1 619 P06 547 | ✓ | ✓ |
| Locking nut 1 603 340 040 | ✓ | ✓ |
| Backing flange (spare part number 2 605 703 014) | ✓ | ✓ |
| Auxiliary handle 1 602 025 024 | - | ✓ |
| Voltage 240 V | - | ✓ |
| Voltage 110 V | ✓ | - |
| Two-hole spanner 1 607 950 043 | ✓ | ✓ |
| Two-hole spanner (spare part number 1 607 950 060) | ✓ | - |