

HI VIS FLOATING RUBBER TORCH



5 HOURS RUNTIME	135 METRE BEAM RANGE	140 LUMENS OUTPUT	IP56 DUST+WATER PROOF
------------------------------	-----------------------------------	--------------------------------	------------------------------------

- » 140 Lumen White Seoul LED
- » Synthetic industrial grade rubber housing
- » Floats beam upright in water
- » Optical Beamaster lens for beam penetration
- » Easy push micro switch operation
- » Ultra tough polycarbonate reflector
- » IP56 dust and water proof
- » Textured handle for extra grip
- » Reinforced anti-roll head

BATTERY 4 x AA batteries (not included)
WEIGHT 301g (without batteries)
DIMENSION 85 x 215mm



BEAMASTER
LENS



MOULDED GRIP HANDLE



EASY PUSH BUTTON MICRO SWITCH



OPTICAL BEAMASTER LENS



WATER PROOF