


## Parts Information: Trolley Jack 3tonne Standard Chassis Model No: 3010CX.V2



Item	Part No.	Description
1	3010CX.01	SIDE PLATE
2	3010CX.02B	WHEEL,FRONT FIXED (95x19x42)
3	FWM18.S	FLAT WASHER M18 SINGLE
4	3010CX.04	CIRCLIP (ID 18MM)
5	3010CX.05	BOLT LINK M16X23
6	3010CX.06	LIFT ARM
	3010CX.V2-06A	SIDE ARM (not shown)
7	3010CX.07	SADDLE
8	3010CX.08	RAISE ARM SUPPORT
9	3010CX.09	C-RING (S25)
10	3010CX.10	GREASE NIPPLE 6mm
11	3010CX.11	C-RING (S25)
12	3010CX.12	LINK SUPPORT
13	3010CX.13	PIN (4x40)
14	3010CX.14	SPRING
15	3010CX.V2-15	POWER UNIT ASS'Y (BLACK)
16	3010CX.16	BOLT
17	SWM18.S	SPRING WASHER M18 ZINC (SINGLE)
18	3010CX.18	TORSION SPRING
19	3010CX.V2-19	HANDLE SOCKET (BLACK)
20	3010CX.20	HANDLE BOLT M12X13
	3010CX.20A	HANDLE BOLT M12X14

Item	Part No.	Description
21	SN10.S	STEEL NUT M10 ZINC DIN934(SINGLE)
22	SWM10.S	SPRING WASHER M10 ZINC (SINGLE)
23	3010CX.23	TIPPING GEAR
24	3010CX.24	PIN (2.5x15)
25	3010CX.25	GEAR SHAFT
26	3010CX.26	HANDLE GRIP
27	3010CX.27	SCREW (M6x35)
28	3010CX.28	HANDLE, LOWER
29	3010CX.29	HANDLE, UPPER
30	3010CX.30	BOLT M17.5X30
31	3010CX.31	REINFORCEMENT SHAFT
32	3010CX.32	LOCK WASHER (12mm)
33	3010CX.33	HEX NUT
34	SWM12.S	SPRING WASHER M12 ZINC (SINGLE)
35	SCB1225.SB	SOCKET HEAD CAP SCREW M12x25 BLACK
36	3250LE.04	WHEEL,CASTOR,BLACK,SINGLE BOLT FIXING (60x7x28x85)
37	3010CX.37	HEX HALF NUT
38	SWM16.S	SPRING WASHER M16 ZINC (SINGLE)
39	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
40	SWM12.S	SPRING WASHER M12 ZINC (SINGLE)
	3010CX.RK	REPAIR KIT (not shown)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534


Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR 01284 757500 

sales@sealey.co.uk

🐑 www.sealey.co.uk



## Parts Information: Trolley Jack 3tonne Standard Chassis Model No: 3010CX.V2



Item	Part No.	Description
1	3010CX.P01	TOP CAP
2	3010CX.P02	O-RING (29.6x3.5)
3	3010CX.P03	SEAL
4	3010CX.P04	RESERVOIR
5	3010CX.P05	OIL FILLER PLUG
6	3010CX.P06	PISTON ROD
7	3010CX.P07	C-RING
8	3010CX.P08	PISTON HEAD
9	3010CX.P09	BOWL WASHER WHITE PLASTIC
10	3010CX.P10	O-RING (32.8x4.6)
11	3010CX.P11	OIL CYLINDER
12	3010CX.P12	NYLON SEAL
13	3010CX.P13	O-RING (46.5x2.4)
14	3010CX.P14	BASE PLATE
15	3010CX.P15	O-RING (15.6x2.6)
16	3010CX.P16	SPLIT WASHER PLASTIC
17	3010CX.P17	PUMP CORE
18	SB-6.0	STEEL BALL 6.0mm
19	3010CX.P19	RESET PLUNGER

Item	Part No.	Description
20	3010CX.P20	OIL DRAIN VALVE STEM
21	3010CX.P21	O-RING (12.5x1.8)
22	3010CX.P22	OIL DRAIN VALVE SEAT
23	3010CX.P23	OIL DRAIN VALVE GEAR
24	3010CX.P24	SPRING WASHER (8mm)
25	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
26	SB-6.0	STEEL BALL 6.0mm
27	SB-9.0	STEEL BALL 9.0mm
28	3010CX.P28	SEALING WASHER
29	3010CX.P29	SOCKET CAP SCREW (M12x20)
30	SB-4.0	STEEL BALL 4.0mm
31	3010CX.P31	BALL VALVE SEAT(C/W STEEL BALL 4MM)
32	3010CX.P32	PRESSURE REGULATING SPRING
33	3010CX.P33	PRESSURE ADJUSTING SCREW
34	3010CX.P34	RELIEF VALVE SEALING RING
35	3010CX.P35	RELIEF VALVE SCREW
36	3010CX.P36	GUIDE PLATE
37	3010CX.P37	O-RING (18.8x2)

**NOTE**: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. **IMPORTANT**: No liability is accepted for incorrect use of product.

sales@sealey.co.uk

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR

🛛 🕤 www.sealey.co.uk