

K Type Surface Temperature Thermocouple

THERMOCOUPLE WITH CERAMIC TIP AND COILED ELEMENT



Stainless steel sheath with a moulded handle and 1.50metres of coiled extension cable terminated in a miniature thermocouple plug.

- Surface temperature fast response thermocouple with ceramic tip and coiled element
- Ceramic Tip
- Maximum Temperature: +900°C
- Probe 7.9mmØ x 100mm long
- Coiled element diameter 5.5mm

T/C Type	Manufacturer's Part Number	Rapid Part Number
K	XE-3818-001	90-2755