TM-308 12mm Digit Stopwatch



PRODUCT DESCRIPTION

Housed in an impact resistant ABS case this stopwatch is easy to use for timing single events. It is simple to use having 3 function buttons, Stop/Start, Lap/Reset & Mode Selection.

- 1/100 sec (for first 30 minutes), 1 second thereafter
- Calendar & time (12/24-hr format)
- · Daily alarm
- Hourly chime
- Water and shock resistant structure
- Case size: 72 x 64 x 20mm
- Supplied with battery (APL-13) and neck cord

TECHNICAL SPECIFICATION

Capacity	23Hrs 59Min's 59Sec's
Resolution	1/100 sec. for first 30 minutes, 1 Second thereafter
Accuracy	±0.5 Sec in 24Hrs
Power	1.5V Button Cell Battery (APL-13)
Dimensions	72 x 64 x 20mm
Weight	60g

CALIBRATION INFORMATION

Calibration Certificate Issued at 5 points; 10mins, 15mins, 30mins, 45mins & 60mins. Additional Points at:

£4.00 per point