FKS-6000 6000g x 1g Weighing Balance







PRODUCT DESCRIPTION

These precision weighing balances have an impact-resistant ABS plastic case and weighing pan, a splash-proof protective cover and non-slip rubber feet. The balance can be either battery or mains powered.

- Weighs in Kg, g, lb, or oz.
- Impact-resistant ABS case with non-slip rubber feet
- Splash-proof protective cover
- 175 x 160mm weighing pan
- 20mm Hi-Contrast LCD display with Backlight
- Automatic backlight when weight is added to the pan
- · Zero tracking ensures stable and repeatable readings
- Tare facility over the full range and can be actioned several times throughout a weighing cycle
- Plus/Minus weighing
- Low Battery indication
- Auto Power Off after 1.5 minutes of no activity
- · Supplied with user guide and batteries
- 2 year warranty

TECHNICAL SPECIFICATION

6000g
1g
±2g
6 x 1.5V AA Alkaline Battery (LR-6)
or AC/DC Mains Power Adaptor (APW-100)
230 x 180 x 50mm (Unit) 175 x 160mm (Pan)
0.9Kg

CALIBRATION INFORMATION Issued at 5 Points:

1Kg, 2Kg, 3Kg, 4Kg, and 5Kg Additional Points at: £10.00 per point