

Product Specification PDF

| | |
|-------------------|------------------------------------|
| Date | Correct as of 16th Oct 2019 |
| Brand | C.K |
| Product | T9505 |
| Description | LED Hand Torch 100 Lumens |
| Barcode | 5013969977523 |
| Commodity code | 8513100000 |
| Country of origin | CN |



| | |
|----------------------|---|
| Features & Benefits | ~ High power 100 lumen CREE XP-E R3 LED ~ 3 lighting modes: High, Dimmed, Flash ~ One-handed Rapid Slide Focus mechanism (RSF) ~ Spot (x1) to Flood (x6) ~ Beam intensifying plano-convex optical lens ~ Robust high grade aluminium body ~ Water & dirt resistant, tested to IP64 ~ Battery life: High ~ 3hrs, Dimmed ~ 7hrs ~ Maximum range: 80 m ~ Battery 1 x AA (Not supplied) |
| Applicable Standards | IPx4 |
| Health & Safety | None applicable |
| Warranty | C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered. |

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 6 | 24 |
| Width mm | 25 | 123 | 130 | 300 |
| Depth mm | 97 | 27 | 190 | 350 |
| Height mm | 30 | 177 | 145 | 220 |
| Weight | 80 | 110 | 724 | 3.6 |
| Packaging Information | Card use | Card | Box | Case |
| | Card gms | 11 | 64 | 675 |
| | Plastic use | Clamshell | 0 | - |
| | Plastic gms | 19 | 0 | 0 |
| | Metal use | 0 | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | 0 | 0 | - |
| | Timber gms | 0 | 0 | 0 |