



**NOTE:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

**IMPORTANT:** No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

**WARRANTY:** Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Parts Information:  
**Compressor 24ltr Direct Drive 2hp**  
**Model No: SAC2420A & SAC2420APK**

Item	Part No.	Description
1	SAC2420EV2.01	Crankcase
2	SAC2420EV2.02	Crankshaft
3	SAC2420EV2.03	Socket Cap Bolt M8x22 (L/H Thread)
4	SAC2420EV2.04	Gasket Seal
5	SAC2420EV2.05	Crankcase Cover
6	SFS610.S	Hex Head Flange Bolt M6 x 10 Zinc
7	SAC2420EV2.07	O-Ring
8	SAC2420EV2.08	Oil Sight Glass
9	SFS618.S	Hex Head Flange Bolt M6 x 18
10	SAC2420EV2.10	Breather
11	SAC2420EV2.11	Connecting Rod
12	SAC2420EV2.12	Retaining Clip
13	SAC2420EV2.13	Piston Pin
14	SAC2420EV2.14	Piston
15	SAC2420EV2.15	Piston Rings (Set of 3)
16	SAC2420EV2.16	Cylinder Gasket
17	SAC2420EV2.17	Cylinder
18	SAC2420EV2.18	Spring Washer
19	SAC2420EV2.19	Bolt
20	SAC0610EV2.17	Valve Gasket
21	SAC2420EV2.21	Valve Plate (Set of 2)
22	SAC2420EV2.22	Valve Reed
23	SAC2420EV2.23	Valve Plate Gasket
24	SAC2420EV2.24	Cylinder Head Gasket
25	SAC2420EV2.25	Elbow Exhaust 3/8"Bsp Male x 2
26	SAC2420EV2.26	Cylinder Head
27	SAC2420EV2.27	Bolt
28	SAC2420EV2.28	Air Filter
29	SFS614.S	Hex Head Flange Bolt M6 x 14 Zinc
30	SAC2420EV2.30	Baffle
31	SAC2420EV2.31	Washer
32	NLN5.S	Nyloc Nut M5 Zinc
33	SAC2420EV2.33	Thermal Cut-Out
34	SN8.S	Steel Nut M8 Zinc
35	SAC2420EV2.35	Capacitor
36	SAC2420EV2.36	Washer
37	SAC2420EV2.37	Spring Washer
38	SAC2420EV2.38	Bolt
39	SAC5020EV2.39	Cover, Pump
40	MSP516.S	Machine Screw Pan Head Phillips M5X16mm (Single)

Item	Part No.	Description
41	SAC2420EV2.41	Ext Circlip 15.6mm Od.
42	SAC2420EV2.42	Fan
43	SAC2420EV2.43	Rear Bearing Case
44	B/6202-2RS	Bearing 6202-2RS
45	SAC2420EV2.45	Stator
46	SAC2420EV2.46	Rotor
47	B/6204-2RS	Bearing 6204-2RS
48	SAC2420EV2.48	Oil Seal
49	SAC2420A.49	Tank 24ltr
50	SN10.S	Steel Nut M10 Zinc
51	FWM10.S	Flat Washer M10 Zinc
52	SAC2420EV2.52	Wheel,Fixed Plastic (D:120 W:30 B:12)
53	SAC2420EV2.53	Wheel Bolt
54	SAC2420EV2.54	Drain Valve 3/8"Bsp Male
55	SS825.S	Hex Head Set Screw M8 x 25 Zinc
56	FWM8.S	Flat Washer M8 Zinc
57	SAC2420EV2.57	Foot
58	FWM8.S	Flat Washer M8 Zinc
59	SN8.S	Steel Nut M8 Zinc
60	SAC2420EV2.60	Handle Grip
61	SAC2420EV2.61	Exhaust Pipe
62	SAC2420EV2.62	Safety Valve 1/4" Bsp 8Bar
63	SAC5030VE2.71	Pressure Switch 20Amp 12Bar 175Psi
64	SAC2420EV2.64	Regulator
65	SAC2420EV2.65	Air Flow Coupling 1/4"Bsp Male
66	SAC2420EV2.66	Pressure Gauge 180Psi Back Fitting D:42mm
67	SAC2420EV2.67	Union 1/4"M-1/4"M 32mm Long
68	SAC2420EV2.68	Pressure Gauge 180Psi Back Fitting D:52mm
69	SAC2420EV2.69	Unloading Pipe
70	SAC2420EV2.70	Brass Nut Deep
71	SAC2420EV2.71	Check Valve
72	SAC2420EV2.72	Power Lead
--	SAC2420EV2.P	Complete Pump
		<b>4pc Air Accessory Kit (part 73) (SAC2420APK ONLY)</b>
	SA332	Tyre Inflator with Gauge
	SA334	Air Blow Gun
	SA335	PE Coiled Air Hose 5m x Ø5mm with 1/4"BSP Unions
	SSG501	Spray Gun Gravity Feed 2.2mm Set-Up

**NOTE:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

**IMPORTANT:** No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

**WARRANTY:** Guarantee is 12 months from purchase date, proof of which will be required for any claim.

**Sealey Group**, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk