Kit Order Code	85-1232	85-1234	85-1236	85-1238	85-1240
Description	ER30 Toolkit	CS18 Toolkit	XS25 Toolkit	Gascat 60 Toolkit	Gascat 120 Toolkit
ER30, 30W 230V soldering iron with PVC cable	<ul> <li>✓</li> </ul>				
CS18, 18W 230V soldering iron with silicone cable		<ul> <li>✓</li> </ul>			
XS25, 25W 230V soldering iron with silicone cable			<ul> <li>✓</li> </ul>		
Gascat 60 soldering iron with flint-wheel ignition				<b>v</b>	
Gascat 120 soldering iron with auto-ignition					<ul> <li>✓</li> </ul>
Flat-pack metal soldering iron stand	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Spare soldering tip 0.5mm - straight	<ul> <li>✓</li> </ul>				
Spare soldering tip 0.5mm - angled	<ul> <li>✓</li> </ul>				
Spare soldering bit 1100 2.3mm		<ul> <li>✓</li> </ul>			
Spare soldering bit 1105 0.5mm		<ul> <li>✓</li> </ul>			
Spare soldering bit 50 2.3mm			<ul> <li>✓</li> </ul>		
Spare soldering bit 55 0.5mm			<ul> <li>✓</li> </ul>		
Gas soldering tip				<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>
Gas Flame tip				<b>v</b>	<ul> <li>✓</li> </ul>
Hot air tip (for heat-shrinking)				<b>v</b>	
Hot knife tip					<ul> <li>✓</li> </ul>
Sponge tray				<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>
2m tube of lead-free solder	<ul> <li>✓</li> </ul>	V	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Desoldering pump	<ul> <li>✓</li> </ul>	V	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Digital mulitimeter with battery		<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Pair of mini cutters	<ul> <li>✓</li> </ul>				
Pair of mini pliers	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Screwdriver with flat blade	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Screwdriver with cross blade	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	<ul> <li>✓</li> </ul>
Tape measure 2m x 16mm	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<b>v</b>	~	<ul> <li>✓</li> </ul>
Auto-lock blade knife	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	~	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>
Hex allen key set: 1.5 to 6mm	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	<ul> <li>✓</li> </ul>	~	<ul> <li>✓</li> </ul>
Weight	765g	860g	900g	780g	850g
Dimensions	285 x 180 x 50mm				

## ER30 iron details

Nominal Power - 30 watts Supplied with nickel plated bit PVC cable CE marked

**CS18 iron details** Nominal Power - 18 watts Supplied with long-life iron plated bit Antex 1100 bit is fitted to this iron (2.3mm) Use Antex 1100 series replacement bits Burn-proof silicone cable CE marked

Gascat 60 iron details Powered by Butane gas (lighter fuel) Nominal Power - 60 Watts Soldering tip fitted Flintwheel ignition Refillable 1 hour (approx) run-time between refills Temperature adjustable on body of the tool Multifunction tool Other tips available

## XS25 iron details

Nominal Power - 25 watts Supplied with long-life iron plated bit Antex 50 bit is fitted to this iron (2.3mm) Use Antex 50 series replacement bits Burn-proof silicone cable CE marked

## Gascat 120 iron details

Powered by Butane gas (lighter fuel) Nominal Power - 120 Watts Soldering tip fitted Piezo auto-ignition Refillable 2 hours (approx) run-time between refills Temperature adjustable on body of the tool Multifunction tool Other tips available