

# Material Handling



Ladders	285
Steps	285
Trolleys	284

## SEALEY



[www.rapidonline.com/sealey](http://www.rapidonline.com/sealey)

## DRAPER<sup>®</sup>



[www.rapidonline.com/draper](http://www.rapidonline.com/draper)

Full range of Material Handling products available at:

**[www.rapidonline.com](http://www.rapidonline.com)**

## Trolleys



### LoadAll™ Board Trolleys



The Armorgard LoadAll™ Board Trolley saves space, provides easy handling and protects materials from damage, whilst in transport. Whether in the yard, on the delivery truck or on site, transporting large sheets of board has never been easier. Specially designed for storing and transporting plasterboard and other large-sheet materials.

- Available in three sizes

Capacity	Size (mm)	Order code	1+
750kg	550 x 1350 x 1130mm	<b>95-0976</b>	540.00
1000kg	730 x 1250 x 1410mm	<b>95-0974</b>	750.00
1500kg	900 x 2100 x 1550mm	<b>95-0975</b>	1250.00

571504



### Hydraulic Platform Trucks

These heavy-duty hydraulic platform trucks from Sealey are fitted with wheels and castors for easy rolling over rough workshop and warehouse floors. They may also be used as mobile service benches.



- Fitted with 2 fixed and 2 swivel composite wheels
- Swivel wheels fitted with foot-operated brake
- One-piece hydraulic unit controlled by large rear mounted foot pedal
- Safety release mechanism positioned on handlebar for smooth controlled descent and safety bars to prevent inadvertent lowering (except **89-1816**)
- Supplied with non-slip platform cover for added load security (except **89-4593**)

Capacity	Order code	1+
150kg	<b>89-4515</b>	235.27
300kg	<b>89-1815</b>	390.00
500kg	<b>89-1816</b>	454.03
1000kg	<b>89-4593</b>	770.00

304827

## Help

Visit our online help centre

[www.rapidonline.com/help](http://www.rapidonline.com/help)



### 3-Level Composite Workshop Trolleys

Composite garage workshop trolley with each shelf having a capacity of 40kg. Walls on only three sides of each shelf allow easy access when adding or removing items. Four large castors, two locking. May also be used as a janitorial trolley.

- Composite garage workshop trolley with each shelf having a capacity of 40kg.
- Walls on only three sides of each shelf allow easy access when adding or removing items.
- Four large castors, two locking.
- May also be used as a janitorial trolley.

Model	Order code	1+
CX309	<b>89-8710</b>	136.33
CX310	<b>89-8713</b>	204.52

527500



### Mobile Tool & Parts Trolley

Heavy gauge steel construction with lockable sliding top on smooth ball bearing runners. Twin drawers with 35mm ball bearing slides, which are locked when top is closed. Handle and oddments tray at each end. Two fixed wheels and two locking castors. Suitable for tools and parts. Some self-assembly required.

- Heavy gauge steel construction with lockable sliding top on smooth ball bearing runners.
- Twin drawers with heavy-duty 35mm ball bearing slides, which are locked when top is closed.
- Handle and oddments tray at each end.
- Two fixed wheels and two locking castors.
- Suitable for tools and parts.
- Some self-assembly required.

Type	Order code	1+
Black	<b>89-7476</b>	202.00
Red	<b>89-7477</b>	202.00

526610



### Utility Tray Trolleys

These robust tray trolleys are ideal for many applications, including catering, serving, warehouses, garages, workshops, plus general everyday use. The trolleys have formed-aluminium uprights and ribbed plastic shelves for strength, durability and stability.

- Hardwearing 100mm dia. thermoplastic rubber swivel castors (2 with brakes)
- Available with 2 or 3 shelves

Type	Order code	1+
2 shelves	<b>14-1904</b>	126.89
3 shelves	<b>14-1906</b>	183.90

538630



### Heavy-Duty Trolleys

These heavy-duty trolleys from Sealey are ideal for regularly used workshop items such as body repair kits, power tools and bulky equipment too big for a tool chest.

Strong build quality and extra large castors make these trolleys excellent for dismantling smaller vehicle components.

- Ideal for storing welding accessories and tools
- Red colour
- Capacity: 50kg/level

No. of levels	Order code	1+
2	<b>89-1676</b>	78.00
3	<b>89-1677</b>	78.00

302088



### Folding Flatbed Trolleys - 150/300kg

These folding flatbed trolleys 150/300kg from Toptruck are sturdy, manoeuvrable steel trolleys suitable for transporting various goods.

Manufactured to a high standard with non-slip rubber platforms and scuff resistant corners, along with powder coated steel handles. Folds flat for compact storage.

- High quality steel trolleys
- Range includes heavy duty version for uneven terrain
- Foldable for easy storage
- Range includes 230-375mm foldable heights
- Ø 100-200mm wheels available

Size (mm)	Capacity	Order code	1+
810 x 470 x 730	150kg	<b>14-1892</b>	83.60
870 x 608 x 907	300kg	<b>14-1894</b>	116.05
945 x 608 x 907	300kg	<b>14-1896</b>	153.38

538631



### Platform Truck with Sides Pneumatic Tyres 200kg Capacity

Heavy-duty steel with hinged mesh construction. Cushioned grip pull handle with smooth steering action for easy manoeuvrability. Steel centred pneumatic wheels allow transport over the toughest terrain. Drop-down sides, for easy loading, are also removable, allowing use as a flatbed for oversized items. Suitable for a variety of warehouse, office, garden and domestic hauling applications.

- Heavy-duty steel with hinged mesh construction.
- Cushioned grip pull handle with smooth steering action.
- Steel centred pneumatic wheels allow transport over the toughest terrain.
- Drop-down sides, for easy loading, are also removable, allowing use as a flatbed for oversized items.
- Suitable for a variety of hauling applications.
- Cart Size: 930 x 480 x 220mm.
- Model No. CST997

Type	Order code	1+
Platform truck	<b>89-5058</b>	148.00

305470



**SEALEY**

**Platform Truck with Sides Pneumatic Tyres 450kg Capacity**

Heavy-duty rust resistant steel construction. Smooth steering action for easy manoeuvrability with soft rubber gripped handle and pneumatic wheels for easy transportation over the toughest terrain. All four sides drop down using locking pin function for easy loading. Can also be used as a flatbed for transporting oversized items. Fitted with additional removable storage tray for carrying smaller items. Suitable for a variety of warehouse, office, garden and domestic applications.

- Heavy-duty rust resistant steel construction.
- Smooth steering action for easy manoeuvrability with soft rubber gripped handle and pneumatic wheels for easy transportation over the toughest terrain.
- All four sides drop down using locking pin function for easy loading.
- Can also be used as a flatbed for transporting oversized items.
- Fitted with additional removable storage tray for carrying smaller items.
- Suitable for a variety of warehouse, office, garden and domestic applications.

Type	Order code	1+
Platform truck	<b>89-8193</b>	260.00

527149



**SEALEY**

**Platform Truck with 4 Removable Panels 300kg 1200 x 800mm**

Welded construction with 15mm wood composite platform and four removable wire mesh panels. Two fixed wheels and two braked castors for easy manoeuvring and safe loading and unloading. Ideal for warehouse and industrial applications.

- Welded construction with 15mm wood composite platform.
- Four removable wire mesh panels.
- Two fixed wheels and two braked castors.
- Platform Size: 1200 x 800mm.
- Platform Height: 280mm.
- Capacity: 300kg.
- Model No. CST773

Type	Order code	1+
Platform truck	<b>89-5257</b>	390.00

305669



**DRAPER**

**2 Tier Tool Trolley**

Only

**£63.66**

Order code 92-0919

[www.rapidonline.com](http://www.rapidonline.com)



**Free Delivery\***

on all orders over £30 (excl. VAT)  
(UK mainland only)

\* See Terms & Conditions for full details - [www.rapidonline.com/terms](http://www.rapidonline.com/terms)

**Steps**

**SEALEY**

**Heavy-Duty Platform Step**

This safety step from Sealey is a robust, lightweight platform safety step featuring a large 390 x 390mm step surface area. Features 4-way access and anti-slip strips to aid stability when in use. Fitted with four anti-slip pads on each corner to prevent movement when in use.

Unit is brightly coloured and due to its angled design will not tip over, even when weight is on the edges making this model safe to work on.

- Top step size: 530mm<sup>2</sup>
- Base size: 685mm<sup>2</sup>
- Step heights: 200, 380mm
- Capacity: 150kg
- Manufacturer's part KS5

Type	Order code	1+
Safety	<b>89-9753</b>	54.00

555621



**DRAPER**

**Kickstool**

Two level, with spring suspension with instant set down once weight is applied. Three castor wheels. Display carton.

- GS and TUV Approved

Type	Order code	1+
Kickstool	<b>91-4296</b>	68.82

311961



**SEALEY**

**Kick-Steps**

These kick-step from Sealey have three spring-loaded wheels which allow the step to glide over floor, yet sit down firmly on rubber stops when load is applied.

- Available with steel or composite construction

Material	Step heights	Order code	1+
Steel	220, 430mm	<b>89-1872</b>	54.00
Composite	220, 420mm	<b>89-1873</b>	40.00
Composite	210, 430mm	<b>89-0297</b>	61.00

302284



**Ladders**

**SEALEY**

**Aluminium Step Ladders EN131**

These durable but lightweight aluminium step ladders from Sealey have a 150kg capacity.

- EN131 approved
- Anodised aluminium alloy frame
- Deep non-slip steps and wide platform with safety rail allowing plenty of legroom for safe standing
- Ribbed feet give full floor contact for extra stability



No. of treads	Order code	1+
3	<b>89-1451</b>	69.00
5	<b>89-1452</b>	86.00
7	<b>89-1453</b>	114.00

301863

**SEALEY**

**Fibreglass Step Ladders EN 131**



Heavy-duty fibreglass sides with slip resistant aluminium treads. Locking brace bars and anti-slip feet for added stability. Lightweight steps are non-conductive and ideal for site work. Certified to EN 131 standards.

- Heavy-duty fibreglass sides with slip resistant aluminium treads.
- Locking brace bars and anti-slip feet for added stability.
- Lightweight steps are non-conductive and ideal for site work.
- Conforms to EN 131 standards.

No. of steps	Order code	1+
4	<b>89-8088</b>	90.00
6	<b>89-8089</b>	122.00
9	<b>89-8087</b>	156.00

302062

**Pallet Truck (2.5 tonne)**

Only

**£460.00**

Order code 92-0973

[www.rapidonline.com](http://www.rapidonline.com)





**CST992 PLATFORM TRUCK  
300KG CAPACITY**

Rigid platform truck features rubberised deck and bumper strip. Handles fold flat for ease of storage. Suitable for a variety of warehouse, office and domestic applications.

Model No	CST992
Capacity:	300kg
Nett Weight:	14.23Kg
Overall Height:	870mm
Platform (W x D):	605 x 910mm
Platform Height:	185mm
Wheel Size:	Ø125mm

£116.00

Order code 89-1646

**CX309 3-LEVEL  
COMPOSITE WORKSHOP  
TROLLEY**

Composite garage workshop trolley with a 40kg capacity per shelf. Walls on only three sides of each shelf allow easy access when adding or removing items. Four large castors, two locking. May also be used as a janitorial trolley.

£136.33

Order code 89-8710

Model No	CX309
Capacity:	40kg/Level
Nett Weight:	9.99Kg
Overall Size (W x D x H):	750 x 460 x 980mm
Shelf Size (W x D):	625 x 420mm

