

Protective Workgear & Equipment



Aprons	292
Boots	292
Fume Extraction	288
Gloves	290
Safety Goggles	289

Stealth 7000™ Safety Glasses Clear Frame Anti Scratch HC Lens



£3.97

Order code 87-3114

CX105 Trolley – 2-level Heavy-duty

SEALEY



£78.00

Order code 89-1676

Full range of Protective Workgear & Equipment products available at:

www.rapidonline.com

BenchVent

The Bench Ventilation Company

BenchVent bench top units help protect pupils and staff from the fumes associated with GCSE, A Level, and higher education classroom experiments.

BenchVent is one of the first British companies to design and manufacture products specifically addressing the fume extraction requirements of school science laboratories.

Built in the UK, BenchVent offers an industry-leading lifetime guarantee for complete peace of mind. All units conform to the guidance of the Health and Safety Executive CoSHH regulations.



Order Code	Model	Description	Air Volume cap	Size	1+
87-5500	BV300S	Glue Spray Air Filtration Unit	325m ³ /hr	A3	£333.69
87-5501	BV200S	Glue Spray Air Filtration Unit	325m ³ /hr	A2	£384.46
87-5504	BV300S-D	Air Extraction Unit	355m ³ /hr	A3	£323.00
87-5502	BV200H	Air Filtration Hoods & Spray Booth	325m ³ /hr	A2	£692.37
87-5503	BV100H	Air Filtration Hoods & Spray Booth	650m ³ /hr	A1	£937.71
87-5505	BV200H-D	Air Extraction Spray Booth	355m ³ /hr	A2	£723.53
87-5506	BV100H-D	Air Extraction Spray Booth	710m ³ /hr	A2	£1094.56
87-5521	BV550S-D	Fume and Vapour Extraction Unit	355m ³ /hr	510x360mm	£684.08
87-5517	BV570H-C	Small Desktop Fume Cabinet	202m ³ /hr	570x465mm	£822.75
87-5513	BV500S-C	Desk/Bench Top Fume Cabinet	325m ³ /hr	575x385mm	£1078.34
87-5514	BV700S-C	Desk/Bench Top Fume Cabinet	650m ³ /hr	515x785mm	£1595.88
87-5519	BV660H-D	Fume Extraction Hood & Cabinet	355m ³ /hr	680x600mm	£950.56
87-5520	BV930H-D	Fume Extraction Hood & Cabinet	710m ³ /hr	960x740mm	£1378.09
87-5515	BV660H-C	Fume Filtration Hood & Cabinet	355m ³ /hr	A2	£1238.05
87-5516	BV930H-C	Fume Filtration Hood & Cabinet	710m ³ /hr	A2	£1896.30



Spare & replacement
filters available

For full details and technical specifications visit
www.rapidonline.com

Safety Goggles

PULSAFE



Bionic Faceshields/Visors - Clear

A range of bionic faceshields and visors from Pulsafe providing maximum visibility. Ideal for various industries, including building, chemical, manufacturing, paint spraying and welding.

- Visor: clear
- EC Category PPE 2
- EC Certificate Number EC1215

Type	Features	Order code	1+
Shield, clear	Acetate	63-9422	36.58
Visor, clear	Acetate	63-9424	9.61

559434

PULSAFE

V-Maxx Vent Goggles Clear Lens



These goggles from Pulsafe has a sporty style for increased wearer acceptance, providing 180° field of vision for distortion free peripheral vision. Designed to fit a wide variety of workers and can be worn over prescription eyewear and with half-mask respirators

- Elastic headband
- Rotating strap attachments
- Shade lens colour: clear
- Lens coating: FogBan
- Shade lens material: PC
- Headband clip: elastic
- Body: indirect ventilation
- EC Category PPE: 2
- EC Certificate Number: EC927

Type	Order code	1+
Chemis indirect vent	63-8796	9.34

558432

bolle SAFETY

Overlight OTG Goggles - Clear



Overlight Goggles are a new generation of OTG (over the glasses) and fit over all standard prescription frames. They have a compact, lightweight design with pivoting temples. The optical class 1 polycarbonate lenses have an anti-scratch and anti-fog coating.

Conform to Standard: EN 166/170 1Ft.

Type	Order code	1+
Overlight goggles	95-2901	5.30

572409

bolle SAFETY

SLAM Safety Glasses

The SLAM Safety Glasses have a modern design, with excellent fitting, to provide both protection and comfort. The spectacles have a wraparound fit to provide a panoramic visual field. The lenses have an anti-scratch, anti-fog coating and the arms feature comfortable temples.



95-2922 SLAM Safety Glasses have ESP (Extra Sensory Perception) lenses. This is an innovative coating to reduce dazzle and the harmful affects of blue light. The ESP coating filters: 57% of blue light, 99.99% of UVA/UVB and transmits 64% of visible light.

Specification

- Lens Type: ESP, Anti-Fog and Anti-Scratch.
- Lens Conforms to: EN1661F/EN170-UV 2C-1.2
- Frame Conforms to: EN166FT.

Type	Order code	1+
ESP	95-2922	6.98
Smoke	95-2924	5.90
Clear	95-2925	5.46
Yellow	95-2926	5.90

572417

uvex

Carbonvision Safety Goggles - Black/Grey - Clear Lens



These carbonvision safety goggles from uvex have been designed with a low profile, wraparound shape, innovative frame, strap and material. High tech materials combine hard and soft components which adapt to wearer's face creating soft, effective seal around the eyes, while the soft seal protects against dust, splashes and mechanical hazards.

Easy and hygienic to clean due to detachable frame and lens concept, plus adjustable high quality strap for individual and pressure-free fit. The uvex permanent supervision extreme lens coating also offers excellent anti-fog performance preventing goggles from steaming up.

- High-quality, long-lasting headband
- Robust frame with flexible soft components
- Outstanding seal and splashproof protection
- Colour: black/grey
- Lens: PC clear/UV 2-1.2
- uvex supervision extreme
- Manufacturer's part **9307.375**

Type	Order code	1+
Safety goggles	63-8517	12.06

559537

COBRA Safety Glasses - ESP



Only **£10.31**
Order code 95-2876
www.rapidonline.com

bolle SAFETY

Kitting Service

Don't forget we offer a bespoke kitting service
education@rapidonline.com

JSP

Martcare M9400 Wraplite Clear Hardia™ Anti-Scratch Lens



These Martcare Wraplite, single lens, wrap-around safety spectacles from JSP are comfortable and lightweight. Their one-piece lens gives an excellent field of vision.

The lens offers protection against low energy, high speed particles at 45m/s (101 mph). The optical qualities of the lens comply with the requirements of optical class 1 (highest).

- Wrap-around design
- Lightweight, one-piece polycarbonate lens
- Blocks 99.9% of ultraviolet radiation
- Conforms to **EN166 1F**
- **JSP type M9400, ASA718-161-100**

Type	Order code	1+
M9400 safety specs	87-0915	2.30

564678

JSP

Martcare M9100 Wraparound Safety Spectacle with Clear HC Lens



A wrap-around, sports style eyeshield for wide vision and complete protection.

- Moulded nose piece for added comfort
- Sideshields and adjustable arms
- Cord attachment point
- Conform to **EN166.1**
- **JSP type ASA240-021-100**

Type	Order code	1+	10+	50+
Wraparound spectacle	87-3178	2.37	2.32	2.04
Wraparound spectacle	87-3178	2.37	2.32	2.04

178129

JSP

Junior Laboratory Spectacles



High quality lightweight junior spectacles with smaller frame, ideal for children and people with small facial features.

- Scratch resistant lens
- Can be worn over most glasses
- Conforms to **EN166**

Type	Order code	1+	10+
Junior spectacles	87-0914	3.86	3.74
Junior spectacles	87-0914	3.86	3.74
Junior spectacles	87-0914	3.86	3.74

72695

No minimum order value
UK mainland only



Martcare Indirectly Ventilated Safety Goggles

These Martcare indirectly-ventilated goggles from JSP are ideally suited for general-purpose eye protection due to their economical pricing and simplicity of use. The indirect ventilation system of the JSP Martcare goggles means that dust or liquid cannot directly fall into the goggles and gives additional protection over goggles which simply have perforated frames to allow air flow.

- Clear PVC lens
- Comfortable soft body
- Adjustable elasticated head-strap
- Conforms to **EN 166- 1.B.3.4**



Type	Order code	1+
Martcare goggles	87-3104	2.89



Martcare M9200 Visispec Spectacle with Clear Lens

The JSP Martcare M9200 Visispec is a good all-round safety spectacle offering excellent value for money.

- Clear polycarbonate lens and temples
- Ideal for visitors
- Conforms to **EN 166.1.F**
- **JSP type ASD020-121-300**



Type	Order code	1+	10+	50+
Visispec spectacle	87-3176	1.78	1.67	1.53



Stealth 7000 Safety Spectacles

Sports style safety spectacles offering excellent protection combined with a modern design.

- Ultra lightweight
- Contour design fits well onto smaller faces, suitable for children
- Clear polycarbonate frame and scratch-resistant lens
- Conforms to **EN166.1.F**
- Available in clear and smoke versions

Type	Order code	1+	5+	10+
Stealth 7000 clear	87-3114	3.97	3.81	3.41
Stealth 7000 smoke	87-3122	3.97	3.81	3.41



Safety Glasses

Manufactured from impact resistant polycarbonate, these safety glasses give clear, distortion-free viewing and can be used over conventional spectacles.



Ideal for use when filing, sanding, planing, routing and many other potentially hazardous jobs involving a risk of eye injury from a low velocity impact.

- Conforms to EN166.1.F Specifications
- Display packed
- **Draper type SG1, 51132**

Type	Order code	1+
SG1 safety glasses	91-7230	5.16



TOOLCRAFT Safety Spectacles

A range of safety spectacles from Toolcraft with clear polycarbonate lenses and PVC frames.



- Range of frame colours
- Range of sizes
- Optical class:1
- All models conform to **EN166:2001**

Type	Order code	1+
Clear	65-3188	2.44
Black/clear	65-3189	3.67
Clear/orange	65-3190	3.16
Clear	65-3191	2.44
Black/clear	65-3192	3.95



TOOLCRAFT Safety Goggles

These Toolcraft safety goggles have a clear polycarbonate lens and a PVC frame.



- Optical class: 1
- Protection class: B
- Available in small and large sizes

Dimensions	Order code	1+
160 x 80 x 76mm	65-3186	3.82
195 x 75 x 85mm	65-3187	5.81

Protector Clear Glasses



Only

£9.90

Order code 84-4230

www.rapidonline.com



Gloves



Medical Advanced Nitrile Powder-Free Disposable Gloves

These Nitrile Powder-Free Examination gloves are an ideal alternative to latex gloves and are recommended for anyone with a type 1 allergy. They contain no natural latex proteins yet have the same wall thickness as a latex glove due to its greater perforation resistance.

Their distinctive blue colour means that they are easily distinguishable from other types of gloves and they are commonly used in hospitals, the nursing sector, medical practitioners in surgeries and the dental sector.

Nitrile Powder-Free gloves have a high resistance to a range of chemicals, and currently Nitrile gloves are believed to be less harmful than Natural Latex Rubber gloves meaning that they are becoming a more popular alternative when protection is required against blood and body fluids during clinical procedures.

- Available in sizes S, M, L and XL
- Box quantity: 100
- **McKinnon type MN100**

Size	Box quantity	Order code	1+
Small	100	87-0929	24.11
Medium	100	87-0931	24.11
Large	100	87-0933	24.11
Extra large	90	87-0943	24.11



Medical Black Nitrile Powder-Free Examination Gloves

These skin-friendly gloves are powder-free, free from latex proteins and accelerant chemicals.

The McKinnon® Nitrile Black is an ideal alternative for people with type I and type IV allergy. The skin-friendly and safe McKinnon® Nitrile Black is an innovative contribution by McKinnon research towards reducing latex allergies in the health sector.

- Free from accelerators (suitable for people with type 4 allergy)
- DOP-Free (DEHP/Diethylhexyl-phthalate)
- Latex-like softness
- Maximum comfort
- Available in sizes S, M, L and XL
- Box quantity: 100
- **McKinnon type MB100**

Size	Box quantity	Order code	1+
Small	100	87-0944	15.74
Medium	100	87-0946	15.74
Large	100	87-0948	15.74
Extra large	90	87-0952	15.74

sempercure® S

Examination Nitrile Gloves - Powder Free - Non Sterile



Powder-free, unsterile, examination gloves made from 100% synthetic latex.

These Sempercure® Nitrile gloves offer resistance and protection at the same time. They are ideal for critical applications like chemical substances and cytostatic agents.

- Good resistance to chemical substances according to chemical resistance list
- Suitable for applications of certain cytostatic agents
- Free from natural rubber latex - perfect for people with type I allergy
- Force at break of 9N - high protection for critical procedures
- Protection from infections - virusproof for users and patients acc. to **EN 455-1 and ASTM F-1671**
- Available in small, medium and large sizes

Size	Box qty	Order code	1+
Small	100	87-0972	14.95
Medium	100	87-0974	18.86
Large	100	87-0976	23.00

semperguard® S

Industrial Nitrile Disposable Gloves



Semperguard Nitrile Classic are very robust disposable gloves made of nitrile with a tried-and-tested design. They are ideal for applications requiring very good tactile properties combined with high resistance.

Classic are very robust disposable gloves made of nitrile with a tried-and-tested design. They are ideal for applications requiring very good tactile properties combined with high resistance.

- CE category III chemicals protective glove for complex risks
- Tried and tested quality product made of nitrile
- Excellent resistance to skin irritants in foodstuffs
- More resilience through special formulation and greater wall thickness
- The problem-solver for single use in applications with an increased need for safety when handling chemicals
- Free from phthalates/softeners and allergenic latex proteins
- Easy to don and particularly skin-friendly through special finishing process
- Signal colour blue - suitable for areas subject to HACCP standards
- Available in 4 sizes S (6-7), M (7-8), L (8-9) & XL (9-10)

Type	Order code	1+
Small (100)	87-0953	23.00
Medium (100)	87-0957	23.00
Large (100)	87-0959	23.00
Extra large (90)	87-0961	23.00

SEALEY

MG795L Mechanic's Gloves Padded Palm Camo



Close fitting gloves suitable for professional workshop use. Palm is padded with cushion points giving added protection against vibration - ideal for use with air powered workshop tools. Camouflage Spandex® back for added user comfort. Hook-and-loop wrist strap. Washable materials.

Type	Order code	1+
Large	94-3162	9.25
Extra-large	94-3163	9.25
Extra-extra-large	94-3164	9.25

WORKY®

Master Cow Split Leather Glove Size 10



Only **£2.85**

Order code 51-7998
www.rapidonline.com

DEWALT

DPG21/3L

Synthetic Padded Leather Palm Gloves



These synthetic padded leather palm gloves from DeWalt have been manufactured with a host of excellent features, including the breathable spandex backs.

- Size: large
- Colour: black and yellow
- Available as fingerless version

Type	Order code	1+
Synthetic gloves	84-3400	17.82
1/2 synthetic gloves	84-3401	17.00

3M

3M™ 7100015974 6700 Reusable Full Face Mask Respirator - No Filters



The 3M 6000 series of full face masks have a low maintenance design and offer maximum comfort and simplicity for high efficiency in your workplace. The exhalation valve helps make breathing easier and gives greater comfort during long use.

One of the lightest, most well-balanced range of respirators available, the 3M 6000 series have easy-to-adjust head straps and have a bayonet connection system enabling them to take a wide range of filters to suit your individual application.

- Small, medium and large sizes available
- Colour: light grey (small), medium grey (medium) and dark grey (large)
- 400g weight - extremely lightweight for high comfort
- Soft, non-allergenic elastomeric facepiece
- Full face lens with broad field of vision - scratch resistant (**EN166:2001 B**)
- Well balanced four strap head suspension - easy to put on and take off
- Patented 3M™ Cool Flow™ Exhalation valve offers reduces breathing resistance
- **Filters not included**, available separately
- **Standard: EN136 class 1**
- **Approval: CE marked**

Size	Order code	4+
Small	65-3968	147.00
Large	51-8326	116.08

JSP

BHT0A3-0L5-N00 Force™ 8 Half Mask Respirator with Press To Check P3 Filters



The Force™ 8 twin cartridge half mask with Typhoon™ valve offers superior low breathing resistance and a 4-point suspension harness with quick release buckles.

The mask is made with a durable thermoplastic rubber offering a superior fit to most face shapes. The mask accepts the full range of low profile Force™; 8 filters giving the Force™ 8 the flexibility to be used for many applications, providing filtering protection against particulates, many gases and vapours.

How can you be sure that you have donned your mask correctly? With the new patent pending Force™ 8 PressToCheck™ filters you can instantly check that you have the correct seal every time.

Don the Mask - Put the straps and harness over your head and pull the straps to a suitably tight and comfortable fit

PressToCheck™ - Press the front and backs of both filter covers together to stop air from entering through the filters

Inhale - No air should come through the mask. Adjust the mask and repeat until it doesn't. Release when seal is made

- Daily Face-Fit Reassurance
- Passes dolomite
- Protection against construction dust
- Improved hygiene
- Inhalation valve for easy maintenance
- Low profile covers protect filters
- Durable thermoplastic rubber mask for superior fit to most face shapes
- Harness has fully adjustable 4-point cradle suspension ensuring an effective facial fit
- CR2 reflective strips create increased visibility in low-light environments for added safety
- Typhoon™ Exhalation Valve with low resistance exhalation valve for easy breathing, with stable mask configuration
- Force™ Filters Cost effective Force™ 8 filters available with low profile angle for minimum visual impairment
- Conforms to EN140 (Face piece), EN14387:2004 (Filter performance), EN143:200 (Filter performance)
- Uses PressToCheck™ P3 R D Filters

Type	Order code	1+
Half mask	87-3292	26.19
Filters - pack of 2	87-3294	10.44

4279 Maintenance Free Half Mask Respirator FFABEK1P3 R D

3M



Only **£31.98**

Order code 51-8321
www.rapidonline.com



Disposable Dust Masks

High quality dust masks from JSP offering up to factor 20x OEL (occupational exposure limit) protection.

- Twin elasticated head straps
- Pliable nose strip to ensure face seal and extra comfort
- Soft, comfortable and lightweight
- Moulded masks in simple, comfortable cup shape
- Valved versions for improved exhalation and comfort
- FFP1 = for fine dusts and mists, solid and liquid based aerosols, assigned protection factor 4 x OEL (occupational exposure limit)
- FFP2 = for fine dusts and mists, solid and liquid based aerosols, assigned protection factor 10 x OEL (occupational exposure limit)
- FFP3 = for very fine dusts, fibres, aqueous and oil based mists, assigned protection factor 20 x OEL (occupational exposure limited)



Style	Pack quantity	Order code	1+
FFP1			
Moulded	20	87-1061	28.69
FFP2			
Moulded, valved	10	87-1032	16.33
FFP3			
Moulded, valved	5	87-3152	18.87

66103

Aprons



Cotton Apron

Heavy duty cotton with neck loop, extra long waist ties and front pocket. Packed in polythene bag with display card.



Type	Order code	1+
Cotton apron	91-4737	4.28

312207



Carpenter's Apron

A traditional style carpenter's apron manufactured from quality linen. Machine washable. Twin front pockets with tie straps.

- One size fits all
- Ideal for hobby & DIY enthusiast



Type	Order code	1+
Carpenter's apron	95-6802	5.52

574106



Disposable Aprons

These child size aprons are an ideal resource for the classroom to protect clothes from glues, paints and all art and craft activities.

- Suitable for **Key Stages 1 & 2** (ages 5 to 11)
- Supplied in **packs of 100**



Type	Order code	1+
Disposable Aprons	06-0270	19.71

71567



Black Rubber Bib Aprons

Basic black rubber aprons, perfect for the chemistry laboratory.

The aprons are comfortable and flexible, waterproof and resistant to most chemicals likely to be used by students.

- Available in medium or large sizes
- Medium: width 685mm (27in.), length 915mm (36in.)
- Large: width 685mm (27in.), length 1065mm (42in.)
- **Eisco RBAP series**



Size	Order code	1+
Medium	52-3595	5.82
Large	52-3594	7.10

565638



Mechanic's Tool Apron 16-Pocket

16-Pocket tool apron perfect for keeping all tools organized and in a reachable location when working at worktable or on a vehicle. Fitted with 16 pockets in varying sizes as well as two loops for use with larger items such as hammers. 2-Way adjustable straps.



Type	Order code	1+
Mechanic's Tool Apron	94-4230	15.00

583361

Pricing

Pricing correct at time of going to press.
For up-to-date pricing visit
www.rapidonline.com



AP-i933 Carpenter's Nail & Tool Bag 10 Pocket

The Kumy's 1933 Carpenter's Nail & Tool Bag is made from heavy-duty top grain leather.

The bag has 10 pockets, including:

- 2 x main nail and tool pockets.
- 2 x additional upper pockets.
- 6 x smaller pockets to fit pliers, nail sets, pencils etc.

The bag also has a metal clip that holds all measuring tape sizes and a hammer loop. It will fit belt sizes up to 70mm (2.3/4in) wide.



Type	Order code	1+
Nail & Tool bag	96-4244	43.00

577361



STST1-80116 Leather Double Nail Pocket Pouch

The Stanley Tools Leather Double Nail Pocket Pouch is perfect for nails and small tools. With easy access pockets, the size and structure of pockets enable easy access. There is also a metal, quick access tape holder. Made from professional, high grade leather (suede) with rivet reinforced stress points and a wide belt slot.



Type	Order code	1+
Nail Pocket Pouch	97-6574	17.79

581132

Boots



Safety Wellington Boots

General work wear boots with metal toecap and mid-sole essential for site work.

- Rubber uppers
- Anti-static with heel shock absorption
- Supplied in pairs
- Manufactured to **EN20345; 2004 S5**
- Available in various UK sizes
- Draper type DSF8/D



UK size	Order code	1+
7	87-9190	21.66
10	87-9196	21.66
11	87-9198	23.19
12	87-9200	23.19

83201