


## DRAWING & CABLE CONSTRUCTION

	<b>SPECIFICATION</b>	P/N	01-0300
	<b>1/0.6TC 0.28MM<sup>2</sup> Equipment Wire Single Core</b>		
Rapid Catalogy Number	GW010300	DATE	13th. Oct., 2016
		SHEET	1/1
IN WALL	NO.	VERSION	A.1
TYPE	N/A	MADE BY	
LENGTH	100Meters	APPROVED BY	
100M SPOOL SIZE	03mm-90*60*60	REVISIONS	
Q'ty/Carton	50 PCS		
Net Weight	22.0 KGS		
Gross Weight	23.0 KGS		
Measure	1.12'		

### MANUFACTURE STANDARD

Proceeding	Description	Material	Thickness	Outer Diameter	Shape	Resistance ohm/km	Electronic Conductivity	Tension KG	Current Max. A	Rated Voltage
Conductor	1/0.60mm	Tinned Copper				61	98%	8	12.4	
Jacket		PVC 105°C	0.31mm	1.2mm±0.1	Round					300V
Printing	N/A									
Printing Contents	N/A									

### Drawing



Remark:  
Current means maximum amps  
for chassis wiring  
PVC=polyvinyl chloride

