

Test Cable

Order code	Manufacturer code	Description
01-0600	n/a	25M REEL RED 55/0.1 EXTRA FLEX
01-0605	n/a	25M REEL BLACK 55/0.1 E/FLEX
01-0610	n/a	25M REEL BLUE 55/0.1 E/FLEX
01-0615	n/a	25M REEL GREEN 55/0.1 E/FLEX
01-0625	n/a	25M REEL WHITE 55/0.1 E/FLEX
01-0630	n/a	25M REEL YELLOW 55/0.1 E/FLEX

Test Cable	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Extra Flexible Cable

55/0.10 C.W.

Technical Specification

Conductor

Conductor Diameter : 55x0.10mm
Wire Material : Bare Copper

Insulation

Insulation Material : PVC Type 2 to BS 6746 (DEF61-12 Part 6)
Insulation Thickness : 0.90mm
Nominal O.D. : 2.8mm \pm 0.1mm

Electrical

Voltage Rating : 1kV
Current Rating : 6 Amps
Temperature Rating : 60°C

Packing

Reel Size : \varnothing 90x60mm
Reel Length : 25m
Reel Weight : 380g

