

### DEF STAN 61-12 PT6-TY 10/0.1

Category Type: Equipment Wire

Test Standard: DEF STAN 61-12 PT6 TY2

## SPECIFICATIONS:

### 1. Conductor

Material: Tinned Copper

Inner Conductor (mm): T0.10×10 (± 0.003)

### 2. Insulation

Material: PVC

Thickness (mm): 0.34 (±0.01)

Diameter (mm): 1.05(±0.05)

Colours: Black, Red, Blue, Brown, Green, Grey, Orange, Pink, Violet, White, Yellow

## Characteristics

Rated Temperature (°C): -15°C to +70°C

Rated Voltage: 250V

Conductor Resist: < 238Ω/1000M @ 20°C, Conductor DC Resist

Min. Insulation Resist: 50 MΩ\*kM @ 20°C, Insulation DC Resist

