

Category Type: Equipment Wire

Test Standard: DEF STAN 61-12 PT6 TY2

SPECIFICATIONS:

1. Conductor

Material: Tinned Copper

Inner Conductor (mm): $10.10 \times 10 (\pm 0.003)$

2. Insulation

Material: PVC

Thickness (mm): $0.34 (\pm 0.01)$

Diameter (mm): $1.05 (\pm 0.05)$

Colours: Black, Red, Blue, Brown, Green, Grey, Orange, Pink, Violet, White, Yellow

Characteristics

Rated Temperature (°C): -15°C to $+70^{\circ}\text{C}$

Rated Voltage: 250V

Conductor Resist: $< 238\Omega/1000\text{M}$ @ 20°C , Conductor DC Resist

Min. Insulation Resist: $50\text{ M}\Omega \cdot \text{kM}$ @ 20°C , Insulation DC Resist

CABLE CONSTRUCTION

