


Equipment Wire

DEF STAN 61-12 PT6-TY 10/0.1

Category Type: Equipment Wire

Test Standard: DEF STAN 61-12 PT6 TY2



SPECIFICATIONS:

1. Conductor

Material: Tinned Copper

Inner Conductor (mm): $T0.10 \times 10 (\pm 0.003)$

2. Insulation

Material: PVC

Thickness (mm): 0.34 ± 0.01) Diameter (mm): 1.05 ± 0.05)

Colours: Black, Red, Blue, Brown, Green, Grey, Orange, Pink, Violet, White, Yellow

Characteristics

Rated Temperature (°C): -15°C to +70°C

Rated Voltage: 250V

Conductor Resist: < 238 Ω /1000M @ 20°C, Conductor DC Resist Min. Insulation Resist: 50 M Ω^* kM @ 20°C, Insulation DC Resist









