

TECHNICAL SPECIFICATIONS

D-Sub Hood:

Material:	UL 94 V-0 Plastic Material
Plating:	Nickel over Copper
Operating Temperature:	-55°C to +110°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (Standard)
Cable O.D:	Up to 11,5mm

High Density D-Sub Solder Cup:

Insulator:	Glass filled TP, UL94 V-0
Shell:	Steel, Tin Plated
Contact pins:	Copper Alloy Gold Flash over Ni.
Stamped & Formed Pins	Class 3, 100 inserts min.
Contact Plating:	Gold flash over Nickel
Operating Temperature:	-55°C to +85°C
Withstanding voltage:	>1000V Rms to 50 Hz for 1 minute
Current Rating:	3A
Insulator resistance:	>5000MΩ min.


Features:

- Available in sizes HD 15-26-44-62
- 360° EMI Shielding
- Re-openable

Grommet Sizes D45PK-P:



...with Connectors from:
Amphenol



Size D45PK-M	Dim A	Dim B	Dim C
9-way	31,0	36,3	15,0
15-way	39,5	40,3	15,0
25-way	53,2	40,3	15,0
37-way	69,7	40,3	15,0

Ordering information:**High Density D-Sub Connector Kits**

Size:	P/N - Kitted:	Product Code - MALE Conn. Kit
HD 15	6355-5017-01	D45PK-M-09+L717HDE15P
HD 26	6355-5017-02	D45PK-M-15+L717HDA26P
HD 44	6355-5017-03	D45PK-M-25+L717HDB44P
HD 62	6355-5017-04	D45PK-M-37+L717HDC62P

Size:	P/N - Kitted:	Product Code - FEMALE Conn. Kit
HD 15	6355-5017-11	D45PK-M-09+L77HDE15S
HD 26	6355-5017-12	D45PK-M-15+L77HDA26S
HD 44	6355-5017-13	D45PK-M-25+L77HDB44S
HD 62	6355-5017-14	D45PK-M-37+L77HDC62S



Encitech AB
Rörkullsvägen 4
SE-302 41 HALMSTAD, Sweden

Tel.: +46-(0)35-15 13 90
Fax: +46-(0)35-15 13 99

www.encitech.com