


PRODUCT

ESD Caution Labels

Yellow ESD caution labels printed with black text onto a yellow background.

TEXT CONTENT

“ATTENTION, OBSERVE PRECAUTIONS FOR HANDLING. ELECTROSTATIC SENSITIVE DEVICES”.

NOTES

Image shown is of 76x38mm labels, layout may vary on different sizes.

FEATURES

- Label type: Self adhesive
- Label size: Various available
- Material: Gloss paper with backing paper for all reel stock applications, suitable for automatic dispensing
- Adhesive: General purpose, strong permanent
- Colour: Yellow with black print
- Pack qty: 1,000 labels per reel
- Design: Industry standard design
- Conforms to EIA & JEDEC-14 standards

PRODUCT CODE	DESCRIPTION	SIZE (mm)	NOTES
055-0002	Yellow ESD Caution Labels	50 x 25	Per Roll
055-0003	Yellow ESD Caution Labels	76 x 38	Per Roll
055-0068	Yellow ESD Caution Labels	16 x 38	Per Roll

Backing Paper	Honey Glassine 65 Yellow transparent glassine backing paper Backing paper for all reelstock applications suitable for automatic dispensing		
	TEST METHOD	VALUE	UNITS
Substance	ISO 536	60	g/m ²
Caliper	ISO 534	53	microns
Tensile Strength MD	ISO 1924	6.3	kN/M
Tensile Strength CD	ISO 1924	2.4	kN/M
Transparency	DIN 53147	50	%
Warranty	Our recommendations are based on our most current knowledge and experience. As our products are used in conditions beyond our control, we cannot assume any liability for damage caused through their use.		

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk

Adhesive	RP51 General purpose strong permanent. Acrylic, waterborne. Good adhesion to all normal substrates, including non-polar surfaces, films and corrugated board. Good low temperature performance.		
PRODUCT CODE	DESCRIPTION	SIZE	NOTES
Tack min	FTM9	14	N
Shear Min	FTM8	1.0	h
PE-Looptack Min	Modified FTM9	10	N
Labelling Temperature Min	-	0	°C
Service Temperature Min	-	-20	°C
Service Temperature Max	-	80	°C
Limitations	Not recommended for labelling highly curved surfaces.		

Roll	Raflabrite IL White woodfree machine coated SC midgloss face paper. Multipurpose label paper, suitable for Indigo digital offset printing.		
PRODUCT CODE	DESCRIPTION	SIZE	NOTES
Substance	ISO 536	86	g/m ²
Caliper	ISO 534	73	microns
Tensile Strength MD	ISO 1924	5.6	kN/M
Tensile Strength CD	ISO 1924	2.7	kN/M
Brightness	ISO 2470/1	88	%
Roughness	ISO 8791 / PPS10	1.1	microns
Opacity	ISO 2471	89	%
Stiffness MD	ISO/DP 5629/1	0.25	mNm
Stiffness CD	ISO/DP 5629/1	0.15	mNm
Printability	Optimized for the HP Indigo WS2000 and WS4000 digital printing presses. Pretesting recommended for conventional printing methods.		
Advantages	Stiffness of the paper offers good application characteristics for large labels. Good strength properties enables matrix stripping of difficult shapes.		

Printing Inks	Water based printing inks.
---------------	----------------------------

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk