






1:1


④

Druckschraube
Sicherungsclip
Schlauchdichtung
Litzendichtung
lose beigelegt

Flachdichtung
16-1166-
lose beigelegt



Montageausschnitt
M1:1



--Alternative mit Abflachung

Technische Daten
siehe 06 6960 0001

Werkstoff / material

Nr. / no

Oberfläche / surface

Index / index



Masse / mass in g

Volumen / volume in cm³

Toleranzen / tolerances

Maßstab / scale

Blattgröße / sheet size

1,5:1

DIN A4

Datum / date

Name / name

Benennung / designation

Gezeichnet
drawn

25.04.19

hauck

Flanschstecker

Geprüft
checked

29.04.19

fhoffmann

flange plug connector


Serie / series

696

4+PE

HEC Schutzschlauchverschraubung

Projektionsmethode 1
first angle projection



Status

50 - Freigegeben

Rev

04

Nummer

21616

Datum

29.04.19

Name

ha

Werkzeug / tool

Zeichnungs-Nr. / drawing no.

09 6491 100 05

beb-intern /
beb-internal

Blatt /
sheet

001

von /
of

Ersatz f /
replaces

Maßeinheit: Millimeter, falls nicht
andere angegeben.
Unless otherwise specified,
dimensions are in millimeters

The reproduction, distribution and utilization of this document
as well as the communication of its contents to others without express
authorization is prohibited. Offenders will be held liable for the
payment of damages. All rights reserved in the event of the grant of
a patent, utility model or design. (ISO 16016)