






1:1

04


A-A

Druckschraube  
Sicherungsclip  
Schlauchdichtung  
Litzendichtung  
lose beigelegt

Flachdichtung  
16-1166-  
lose beigelegt



Montageausschnitt  
M1:1



-- Alternative  
mit Abflachung

Technische Daten  
siehe 06 6960 0001

Werkstoff / material

Nr. / no

Oberfläche / surface

Index /  
index



Masse / mass in g

Volumen / volume in cm<sup>3</sup>

Toleranzen / tolerances

Maßstab / scale

Blattgröße / sheet size

1,5:1

DIN A4

Datum / date

Name / name

Benennung / designation

Gezeichnet  
drawn

25.04.19

hauck

Geprüft  
checked

29.04.19

thoffmann

Serie / series

696

Flanschdose

flange socket

4+PE

HEC Schutzschlauchverschraubung

Werkzeug / tool

Zeichnungs-Nr. / drawing no.

beb-intern /  
beb-internal


Blatt /  
sheet

09 6492 100 05

001

von /  
of

Projektionsmethode 1  
first angle projection



Status

50 - Freigegeben

Rev

04

Nummer  
number

29.04.19

Datum  
date

ha

Name  
name

Ersatz f /  
replaces

Maßeinheit: Millimeter, falls nicht  
andere angegeben  
Unless otherwise specified,  
dimensions are in millimeters

The reproduction, distribution and utilization of this document  
as well as the communication of its contents to others without express  
authorization is prohibited. Offenders will be held liable for the  
payment of damages. All rights reserved in the event of the grant of  
a patent, utility model or design (ISO 10016)