






1:1

③

Druckschraube
Sicherungsclip
Schlauchdichtung
Litzendichtung
Druckring
lose beigelegt

A-A


Flachdichtung
16-1166-
lose beigelegt



O-Ring
16-0210-

O-Ring
16-1284-

Montageausschnitt
M1:1



-- Alternative mit Abflachung

Technische Daten
siehe 06 6960 0001

Werkstoff / material

Nr. / no

Oberfläche / surface

Index /
index

binder

Masse / mass in g

Volumen / volume in cm³

Toleranzen / tolerances

Maßstab / scale

Blattgröße / sheet size

1,5:1

DIN A4

Datum / date

Name / name

Benennung / designation

Gezeichnet
drawn

25.04.19

hauck

Geprüft
checked

29.04.19

thoffmann

Serie / series

696

Flanschdose

flange socket

12P ol

HEC Schutzschlauchverschraubung

Werkzeug / tool

Zeichnungs-Nr. / drawing no.

09 6520 100 12


beb-intern /
beb-internal

Blatt /
sheet

001

von /
of

Projektionsmethode 1
first angle projection



Status
50 - Freigegeben

Rev
rev

21616

29.04.19

ha

Ersatz f /
replaces

Maßeinheit: Millimeter, falls nicht
anderns angegeben
Unless otherwise specified,
dimensions are in millimeters

The reproduction, distribution and utilization of this document
as well as the communication of its contents to others without express
authorization is prohibited. Offenders will be held liable for the
payment of damages. All rights reserved in the event of the grant of
a patent, utility model or design (ISO 16016)