



Part Number	UNIF04015RD
Description	4 Core Standard Fire Resistant Cable
Conductor	Class 1 Solid Copper and over Class 2 Stranded Copper
Insulation	High Performance Fire Resistant Silicone Rubber
Cross Sectional Area	1.5mm
Diameter over Insulation	9.4mm Nominal
Conductor Resistance	12.1 Ω/km at 20°C (nominal)
Insulation Resistance	300MΩ/km at 20°C (nominal)
Voltage Rating	300/500V
Cable Weight	1.4kg reel weight (nominal)
Temperature Range	-40°C to +90°C
Length Supplied	100m +/- 10-12%

* Figure is nominal, exact number of strands used may be lower

