

Order code: 02-1506

Part Number	UNITWA0.5GN500R
Description	UniStrand Green Thin Wall Automotive Cable
Conductor Material	Bare copper
Insulation	PVC
Insulation Radial Thickness	0.4mm *Average
Outer Diameter	1.80 ±0.10mm
Conductor Stranding	7/0.32+/-0.008mm
Conductor Cross Section Area	0.5mm ²
Voltage Rating	60V
Cable Weight	15.32kg per roll
Temperature Range	Max 70°C
Length Supplied	500m +/- 10-12%
Applicable Standards	ISO6722