

Order code: 02-1515

Part Number	UNITWA1.5RD500R
Description	UniStrand Red Thin Wall Automotive Cable
Conductor Material	Bare copper
Insulation	PVC
Insulation Radial Thickness	1.5mm
Outer Diameter	2.40±0.10MM
Conductor Stranding	30/0.25±0.008 MM
Conductor Cross Section Area	1.5mm ²
Voltage Rating	60V
Cable Weight	15.32kg per roll
Temperature Range	Max 70°C
Length Supplied	500m +/- 10-12%
Applicable Standards	ISO6722